

# LED Bulb GU5,3 MR16 3W 12V 4500K 130lm 38° Forever Light

RTV0600008  
5900495881618



Bulb with "stick" cap with narrow angle of light, supplied with 12V. It is used as an auxiliary point source of light, decorative lighting and also furniture and ceiling fixtures. APPLICATION: ? Suspended ceilings ? recesses

## Specification

|                                         |                   |
|-----------------------------------------|-------------------|
| <b>Brand:</b>                           | Forever Light     |
| <b>Energy class:</b>                    | G                 |
| <b>Color temperature:</b>               | 4500K             |
| <b>Thread type:</b>                     | GU5,3             |
| <b>Working voltage:</b>                 | 12V 50Hz          |
| <b>Current:</b>                         | 625 mA            |
| <b>Power consumption:</b>               | 3 W               |
| <b>Lumens number:</b>                   | 130 lm            |
| <b>Diodes number:</b>                   | 4 pcs.            |
| <b>Diodes type:</b>                     | SMD2835           |
| <b>Light angle:</b>                     | 38°               |
| <b>Diameter:</b>                        | 50 mm             |
| <b>Net weight:</b>                      | 26 g              |
| <b>Lifetime:</b>                        | 30 000 h.         |
| <b>Working temperature:</b>             | -20°C up to +45°C |
| <b>Flash point:</b>                     | < 0,5s            |
| <b>Warm-up time:</b>                    | < 1 s             |
| <b>Number of on/off:</b>                | > 15 000          |
| <b>Power factor (PF):</b>               | >0,4              |
| <b>CRI (Ra) factor:</b>                 | > 80              |
| <b>Dimmer:</b>                          | no                |
| <b>Equivalent of an old light bulb:</b> | 25 W              |
| <b>Mercury content:</b>                 | 0 mg              |
| <b>Warranty:</b>                        | 24 month          |
| <b>Certificate:</b>                     | CE ROHS           |



SCAN ME!